


***Technical data for
hand control type DCG14-1H,
DCG control cable D620095 and
DCG motor cable D620090***



CE

Hand control DCG14-1H

The plug can be connected to input HS on all Thomson DCG, AC-063 and AC247 ELS actuator control boxes.

7 × 0,14 mm²
L = 1500

50
138
22
37
30

Indoor use only!

Weight = 0,4 kg

red — 3
brown — 5
blue — 7

DCG control cable D620095

30 2450 7 × 0,14 mm²

The plug can be connected to input HS on all Thomson DCG, AC-063 and AC247 ELS actuator control boxes.

colour: black

50±5

solder view

1 = green
2 = yellow
3 = grey
4 = blue
5 = red
6 = black
7 = white
shell = beige

DCG motor cable D620090

30 2000

The plug can be connected to input M1 and M2 on all Thomson DCG and AC247 ELS actuator control boxes.

colour: black

70±10

1 — green
2 — red
3 — black
4 — brown
5 — purple
6 — yellow
7 — white
8 — white
shell

green —
red —
black —
brown —
purple —
yellow —
white —

red, green, yellow, white (4 × 0,5 mm²)
faston contact 2,8 × 0,8 mm insulated

black, brown, purple (3 × 0,14 mm²)
faston contact 2,8 × 0,8 mm insulated

Note! use red and green for connections to the actuator motor.